




# FILTRA INOX & DESIGN















# FILTRA INOX & DESIGN





\* selon modèle, je nach Modell, niet op alle modellen aanwezig, a seconda del modello, según modelo, conforme o modelo, bazı modellerde, afhængig af model, beroende på modell, kun på noen modeller, mallista riippuen, ανάλογα με το μοντέλο, в зависимости от модели, w zależności od modelu, podle modelu, pod'l'a modelu, modeltCei függCeen, според модела,












2 -






Model	2 L	3 L	4 L
Min.	1,8 l	2,5 l	3,5 l
Max.	2 l	3 l	4 l







Model	2 L	3 L	4 L
Min.	1,6kg	2,2kg	3,1kg
Max.	1,75 kg	2,6 kg	3,5kg





# 3 -







- 4 L +/- 1 000 g
- 3 L +/- 800 g
- 2 L +/- 600 g




- 4 L +/- 900 g
- 3 L +/- 600 g
- 2 L +/- 450 g




# 4 -








	Nb		°C	
		1000 g	<b>1</b> 160°C <b>2</b> 190°C	+/- 9 - 10 min. +/- 5 - 6 min.
		600g	170°C	+/- 14 - 18 min.
		800g	180°C	+/- 12 - 14 min.
		800 g	<b>1</b> 160°C <b>2</b> 190°C	+/- 7 - 10 min. +/- 3 - 6 min.
		400 g	170°C	+/- 12 - 16 min.
		700 g	180°C	+/- 10 - 14 min.
		300 g	170°C	+/- 10 - 15 min.
		600 g	190°C	+/- 12 - 13 min.
		400 g	160°C	+/- 6 - 7 min.
	8 - 9		170°C	+/- 5 - 6 min.
	Nb		°C	
		450 g	170°C	+/- 9 - 13 min.
		900 g	190°C	+/- 10 - 12 min.
		300 g	170°C	+/- 8 - 12 min.
		600 g	190°C	+/- 7 - 9 min.
		250 g	170°C	+/- 8 - 12 min.
		450 g	190°C	+/- 7 - 9 min.
	12		190°C	+/- 5 - 6 min.
		1200g	190°C	+/- 8 - 10 min.
		1000g	190°C	+/- 7 - 8 min.
		800g	190°C	+/- 5 - 7 min.
	10 - 12		190°C	+/- 7 - 8 min.

6 -






7 -





8 -



9 -

